

Specification Sheet

Part Number: 151-14059



RB Adhesive Cable Clamp, 0.20" Max. Bundle Dia, PA66, Natural, 100/pkg

Article Number	151-14059
Type	RB5
Color	Natural (NA)
Features & Benefits	•Simple snap-in design allows for quick and easy installation or removal of cables. •Rubber based adhesive allows for a permanent bond to most surfaces.
Quantity Per	pcs.
Product Description	The RB Adhesive cable clamps are designed with an easy snap-in feature allowing simple installation or removal of cables, pipes or hoses. The rubber based adhesive allows for a permanent bond to most surfaces.

Short Description	RB Adhesive Cable Clamp, 0.20" Max. Bundle Dia, PA66, Natural, 100/pkg
Global Part Name	RB5-PA66-NA
Length L (Imperial)	0.75
Length L (Metric)	19.0
Fixation Method	Pasting / Stick
Variant	Closed
Width W (Imperial)	0.75
Width W (Metric)	19.0
Bundle Diameter Max (Imperial)	0.20
Bundle Diameter Max (Metric)	5.0
Height H (Imperial)	0.24
Height H (Metric)	6.0
Nominal Diameter (Imperial)	3/16
Nominal Diameter (Metric)	5.0

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Adhesive	Synthetic rubber with base of polyethylene foam
Flammability	UL 94 V2 (excluding adhesive)
UV Resistant (Yes/No)	No
Adhesive Operating Temperature	-40°F to +140°F (-40°C to +60°C)
Operating Temperature (Metric)	-40°F to +140°F (-40°C to +60°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909987
Content Unit(BMEcat)	pcs.
Weight (Metric)	3

