



+ CONNECTORS

RECTANGULAR CONNECTOR HOODS



✓ Active

TE CONNECTIVITY (TE)

HD.40.STS.1.29.Z

HDC | [HDC Hood & Housings](#) , [HDC IP 65 Hood & Housing](#)

1-1102566-6

TE Internal Number: 1-1102566-6

[EU RoHS Compliant with Exemptions](#)

[EU ELV Compliant with Exemptions](#)

Accessory Type Hood

Entry Style Side

Locking Device Type Locking Clip

Locking Device Location Housing Bottom

↓ **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

HOOD HD 40 STS1.29.Z

PDF [\(TIFF AVAILABLE\)](#)

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Accessory Type Hood
Product Size 6
Thread Size PG29
Product Type Accessory
HTS Housings and Hoods Yes

Body Features

Entry Style Side
Color Gray
Material Die Cast Aluminum

Mechanical Attachment

Locking Device Type Locking Clip
Locking Device Location Housing Bottom

Dimensions

Height 76 mm [2.99 in]
Width 43 mm [1.69 in]
Length 93.5 mm [3.68 in]

Usage Conditions

Corrosion Protected No

Packaging Features

Packaging Quantity 5
Packaging Method Box

Other

Comment Hood assembly includes cable adapter.

Statement of Compliance

Statement of Compliance
PDF