



Color: white

Technical data		
Marking method		Thermal transfer
Marking		plain
Delivery form		Roll
Delivery form configuration		3000 markers/reel
Printing device		TP 298+
Physical data		
Depth		0.35 mm
Length		12 mm
Mechanical data		
Mounting type		Pushing in
Material data		
Color		white
UV resistance		EN 60068-2-5:2010 Procedure B
Adhesive information		without adhesive
Halogen-free		Yes
Weight		520 g
Fire load		0 MJ
Commercial data		
Product Group		2 (Terminal Block Accessories)
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		DE
GTIN		4045454486044
Customs tariff number		49119900000



Product Classification	
UNSPSC	55121612
eCl@ss 10.0	27-40-06-29
eCl@ss 9.0	27-40-06-29
ETIM 9.0	EC001288
ETIM 8.0	EC001288
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 211-111

↓

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Marking sleeve



[Item No.: 211-112](#)
Nozzles; Length: 12 mm; only for use with 211-110/-111/-120/-121; halogen-free; Cable outer diameter: 1.6 ... 3.2 mm; black



[Item No.: 211-113](#)
Nozzles; Length: 12 mm; only for use with 211-110/-111/-120/-121; halogen-free; Cable outer diameter: 2.2 ... 4.5 mm; black



[Item No.: 211-114](#)
Nozzles; Length: 12 mm; only for use with 211-110/-111/-120/-121; halogen-free; Cable outer diameter: 3.7 ... 5.9 mm; black



[Item No.: 211-115](#)
Nozzles; Length: 12 mm; only for use with 211-110/-111/-120/-121; halogen-free; Cable outer diameter: 5.5 ... 10.0 mm; black