



Part Number : [192040025](#)

Series Number : 19204

Product Category : Splices

Product Description : InsulKrimp 4 Way Splice for 10-12 AWG Wire

Status : Active

Engineering Number : C-2XCX

---

## Documents & Resources

### Drawings

[Drawing 192040025\\_sd.pdf](#)

### Specifications

[Product Specification PS-19902-009-001.pdf](#)


[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Part Details

### General

Status	Active
Category	Splices
Series	19204
Description	InsulKrimp 4 Way Splice for 10-12 AWG Wire
Comments	4 Way Connector
Product Family	Splices
Product Name	4 Way,InsulKrimp
UPC	800753051799

### Electrical

Voltage - Maximum	600V
-------------------	------

### Physical

Barrel Type	Closed
Color - Resin	Natural
Insulation	PVC
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	PVC
Net Weight	7.960/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Temperature Range - Operating	-40° to +105°C
Wire Insulation Diameter	6.35mm max.
Wire Size (AWG)	10, 12
Wire Size mm <sup>2</sup>	3.30-5.00

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Application Tooling

### Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm <sup>2</sup> (Rings, Spades, Hooks, Block Spades and Flanged Spades)	<u>640010100</u>
PremiumGrade Hand Crimp Tool for Insulkrimp Terminals and Splices, 10-22 AWG (Rings, Spades, Hooks, Block Spades and Flanged Spades)	<u>640010300</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050300</u>
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	<u>640160036</u>

---

This document was generated on Jul 29, 2024