

## M17-CCH-BAY-STR-SHLD-6.5-10mm



Image is for illustration purposes only. Please refer to product description.

Part number	21 17 200 0200
Specification	M17-CCH-BAY-STR-SHLD-6.5-10mm
HARTING eCatalogue	<a href="https://harting.com/21172000200">https://harting.com/21172000200</a>

### Identification

Category	Connectors
Series	Circular connectors M17
Type of hood/housing	Cable housing

### Version

Size	M17
Shielding	Shielded
Version	Top entry
Locking type	Toggle locking

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66 / IP67 screwed / locked condition
Clamping range	6.5 ... 10 mm

### Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
Material (seal)	NBR
Colour (seal)	Black
RoHS	compliant
ELV status	compliant



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	IEC 61984 IEC 60664-1
UL / CSA	UL 2237 / 2238 in preparation
Approvals	CE

## Commercial data

Packaging size	1
Net weight	60 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140505674
eCl@ss	27440224 Shell for circular connectors
UNSPSC 24.0	39121405