






APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/19/11	
A		REDRAWN	12/7/12	



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material: Nylon 66, rated UL 94V-0
Insulator color: White
Contacts: Brass, Tin plated
Electrical:
Operating voltage: 250V AC, DC
Current rating: 3A AC, DC (#20, #22AWG)
Contact resistance: 10 Mohms max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Temperature Rating:
Operating temperature: -25°C to +85°C
Environmental:
Lead free, RoHS compliant

Positions: 2 thru 15
A = .098 [2.50] x of Spaces
B = .098 [2.50] x of Spaces +.197 [5.00]

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: .098 [2.50] SHROUDED CRIMP HEADER ASSEMBL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				INCHES				Holes			
.X	±.10	ØXX	±.10	.XX	±.020	ØXXX	±.015	.XXX	±.015	ØXXX	±.010
APPROVALS				DATE							
DRAWN	TW	9/19/11									
CHECKED	AY	9/19/11									
APPROVED											

ROHS
COMPLIANT