

MPC-NCNCJ10020F-NN

MPO Trunk Cable, Multimode, 12 fibers, MPO to MPO, 20 ft

OBSOLETE

Product Classification

Regional Availability	Latin America North America
Portfolio	NETCONNECT®
Product Type	Fiber trunk cable assembly
Product Brand	MPOptimate®
Product Series	MPC

General Specifications

Color, boot A	Black
Color, boot B	Black
Color, connector A	Beige
Color, connector B	Beige
Connector A, quantity	1
Connector B, quantity	1
Interface, Connector A	MPO-12/UPC Female
Interface Feature, connector A	Unpinned
Interface, Connector B	MPO-12/UPC Female
Interface Feature, connector B	Unpinned
Jacket Color	Orange
Total Fibers, quantity	12

Dimensions

Cord Length	6.1 m 20.013 ft
-------------	-------------------

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM1

MPC-NCNCJ10020F-NN

Environmental Specifications

Environmental Space Plenum

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

