



YAV10HNK



YAV10HNK

Copper Compression Lug, Heavy Duty, Ring Tongue with Shroud, 1 Hole w/ Inspection Hole, 12-10 AWG, #8-#10 Stud, Short Barrel, Nickel Plated

Image | Line Art | 3D Model | Video | Customer Drawing

Email Datasheet

Print Datasheet

Specifications

Dimensional	General	Conductor(s)	Physical	Approvals / Certifications	Other Features
Dimensional					
Length (in)				1.04	
Tongue Type				Ring	
Stud Size (in)				#10,#8	
Pad Width (in)				0.38	
General					
Product Description				Copper Compression Lug, Heavy Duty, Ring Tongue with Shroud, 1 Hole w/ Inspection Hole, 12-10 AWG, #8-#10 Stud, Short Barrel, Nickel Plated	
Conductor(s)					
Aircraft Cable Size (Range)				AN 12-AN 10	
Copper Solid Size (Range)				N/A	
Navy Cable Size (Range)				6 (7)-9 (37)	
Copper Stranded (Range)				12-10	
Physical					
Type of Plating				Nickel	
Connector Type				Terminal - Ring	
Plated (Yes or No)				Y	
Approvals / Certifications					
UL Listed				N	
CSA Certified				N	
ROHS Compatible				Compliant	
UL Recognized				N	
CULUS				N	
Industry Standards				UL467	
Other Features					
UPC				7818100929655	