



**Part Number :** [734155190](#)  
**Product Description :** MCX Plug, Right-Angle, Crimp, RG-179 Cable, Die Cast Body, Nickel (Ni) Plated, 75 Ohms  
**Series Number :** 73366  
**Status :** Active  
**Product Category :** RF / Coaxial Connectors



## Documents & Resources

### Drawings

- [734155190 sd.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                                           |
|--------------------|-----------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                                              |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                              |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                                            |
| REACH SVHC         | Contains Lead per D(2023)3788-DC (14 Jun 2023)                                                            |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863                                                             |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

**Part Details**

**General**

|              |                                                                                        |
|--------------|----------------------------------------------------------------------------------------|
| Status       | Active                                                                                 |
| Category     | RF / Coaxial Connectors                                                                |
| Series       | 73366                                                                                  |
| Description  | MCX Plug, Right-Angle, Crimp, RG-179 Cable, Die Cast Body, Nickel (Ni) Plated, 75 Ohms |
| Application  | RF                                                                                     |
| Product Name | MCX                                                                                    |
| Style        | Cable                                                                                  |
| Type         | Microminiature                                                                         |
| UPC          | 822348709366                                                                           |

**Electrical**

|                 |                             |
|-----------------|-----------------------------|
| Frequency       | 6 GHz                       |
| Impedance       | 75Ω                         |
| Power / Voltage | VOLTAGE: 335 Vrms@Sea Level |

**Physical**

|                       |             |
|-----------------------|-------------|
| Cable Attachment      | Crimp       |
| Gender                | Plug        |
| Keying to Mating Part | N/A         |
| Net Weight            | 1.254/g     |
| Orientation           | Right Angle |
| Packaging Type        | Bag         |
| Panel Mount           | No          |
| Panel Mount Method    | N/A         |

|                 |        |
|-----------------|--------|
| PCB Mounting    | N/A    |
| Reverse Polar   | No     |
| Wire/Cable Type | RG-179 |

**Solder Process Data**

|                              |     |
|------------------------------|-----|
| Lead-Free Process Capability | N/A |
|------------------------------|-----|

---

This document was generated on Sep 11, 2025