



C2G  
**Discontinued - 29.5ft (9m) SC-SC 50/125 OM2 Duplex Multimode Fiber Optic Cable - Plenum CMP-Rated - Orange**  
Part No. 37870



Cost-effective solution that provides higher bandwidth and transmission rates and supports longer distances with lower loss than 62.5/125 fiber. Specifically designed for use with today's narrower aperture components, this cable is fully compatible with multimode applications. The plenum rating provides the fire protection required to run this cable within walls and air plenums without using conduit. The patented injection molding process provides each connection greater durability in resisting pulls, strains and impacts from cabling installs.

Each cable is 100% optically inspected and tested for insertion loss before you receive it. A pull-proof jacket design surrounds the popular 50/125 multimode fiber, immune to electrical interference.

Features & Benefits

- Designed to support gigabit ethernet, fibre channel, Infiniband, ATM, and internet protocol applications
- Plenum CMP rated for cable runs through walls and drop ceilings with plenum air space
- Patented injection molding process for greater durability
- Optically inspected and tested for insertion loss
- Pull-proof jacket design, immune to electrical interference

Specifications

General Info			
Product Line	C2G	Color	Orange
UPC Number	757120378709	Country Of Origin	Hong Kong
Application Sector	Commercial, Industrial	Type	Cable
Dimensions			
Cable Length	29.5 ft		
Technical Information			
Fiber Optic Cable Type	Multimode, OM2	Jacket Material	PVC (Polyvinyl Chloride)
Jacket Application	Plenum Rated	Bend Radius	50 mm
Simplex/Duplex	Duplex	Cable Type	Fiber Optic
Jacket Rating	CMP Rated, FT6 Rated	Connector 2	SC Male
Connector 1	SC Male	Fiber Size	50/125