




11	SOCKET CONTACTS	Brass/Au Plated	4
10	SPRING WASHER	PPS/Black	1
9	SPRING	SUS 304/Ni Plated	1
8	LATCH SPRING	SUS 304/Ni Plated	1
7	MACHINED SHELL	Brass/Ni Plated	1
6	INSULATOR	PPS/Black	1
5	MACHINED SHELL	Brass/Ni Plated	1
4	METAL NUT	Brass/Ni Plated	1
3	SPRING WASHER	SUS 304/Ni Plated	1
2	GROUND CONTACT	Brass/Ni Plated	1
1	PUSH LEVEL	Brass/Ni Plated	1
ITEM	DESCRIPTION	MATERIAL/FINISH	QTY

Specification:
Electrical:
Contact resistance: <0.03 ohm
Insulation resistance: >500Megaohm
Dielectric strength: 1000VDC
Rated current: 5A

Mechanical:
Lifetime: Insert & withdraw >5000 cycle
Insertion/withdrawal 6lb Max.

UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE			THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD.. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER			0	FIRST ISSUE		M.H	09-10-12	----		
LINEAR		ANGULAR		REV.			CHANGE DETAILS		BY	DATE	CHG/No		
X ± 0.50		X° ± 1°		CAD FILE: 55010861100110			DRN: M.H		DATE: 09-10-12		TITLE: MINI XLR FEMALE RECEPTACLE CUSTOMER DWG Amphenol Amphenol Australia Pty Ltd, 2 Fireways Blvd, Keysborough, Vic 3173		
X.X ± 0.25		X°X' ± 30'		MATL: MACHINED SHELL			CKD: M.H		DATE: 09-10-12				
X.XX ± 0.10		X°X'X" ± 15'		DO NOT SCALE			FINISH: NICKEL PLATED		APP'D: P.M			DATE: 09-10-12	
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS													
DIMENSIONS IN MILLIMETRES			 THIRD ANGLE PROJECTION			SCALE: 2:1 UOS		PART No: AG4FCE		SIZE: A3		55010861-100-1	
													SHEET 1 OF 1