



Color: ■ yellow Similar to illustration

Technical data	
Suitable	for wire cross-section 25 ... 35 mm²
Marking method	Thermal transfer
Delivery form	Roll
Delivery form configuration	15 m/roll
Printing device	Smart Printer (thermal transfer printer)

Physical data	
Depth	0.185 mm

Mechanical data	
Mounting type	Sliding on conductor
Shrink rate	2:1
Smear resistance	in conjunction with 258-5005 Ink Ribbon

Material data	
Color	yellow
Material	Polyolefin
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	without adhesive
Halogen-free	Yes
Weight	434 g
Fire load	0 MJ



Environmental requirements	
Ambient temperature (storage)	+10 ... +25 °C
Ambient temperature (operation)	-55 ... +125 °C
Relative humidity	45 ... 55 %

Commercial data	
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DK
GTIN	4055143370325
Customs tariff number	39173200900

Product Classification	
UNSPSC	39121703
eCl@ss 10.0	27-40-04-01
eCl@ss 9.0	27-40-04-01
ETIM 9.0	EC001530
ETIM 8.0	EC001530
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 211-505/000-002	

Documentation	
Operating Instructions	
211-502 Information on printing material	128.08.2020pdf1059.74 KB

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com