

Part Number : 1063975301
Product Description : LC2+ Connector High Temperature, Singlemode, 126µm Ceramic PC Ferrule, 1.60mm Simplex Cable, Blue Housing, Straight Boot
Series Number : 86389
Status : Active
Product Category : Fiber Optic Connectors

Documents and Resources

Drawings

1063975301_sd.pdf

Specifications

1063971902-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Fiber Optic Connectors
Series	86389
Description	LC2+ Connector High Temperature, Singlemode, 126µm Ceramic PC Ferrule, 1.60mm Simplex Cable, Blue Housing, Straight Boot
Mode	Singlemode
Product Name	LC2+
UPC	884982286740

Physical

Angled Physical Contact (APC)	No
Boot Color	Red
Boot Type	Straight
Cable Size	1.60mm
Color - Resin	Blue
Ferrule Hole Size	126µm
Ferrule Material	Ceramic
Gender	Plug
Material - Housing	N/A
Mounting Style	Adhesive
Net Weight	1.500/g
Ports	1
Wire/Cable Type	Simplex

Downloaded from Arrow.com.