



Part Number : [1300350071](#)

Product Description : Mini-Change 5 Pole Tee Wye Adapter, Male to Female

Series Number : 130035

Status : Active

Product Category : Industrial Tees and Splitters

Engineering Part Number : DN3200




Documents and Resources

Drawings

[1300350071_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	130035
Description	Mini-Change 5 Pole Tee Wye Adapter, Male to Female
IP Rating	IP67
Product Name	DeviceNet Trunk,Mini-Change
Type	Drop Tee, Drop Wye
UPC	78678841726

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V AC/DC

Physical

Color - Cable Jacket	Gray
Drop Connector	Mini-Change
Drop Gender	Female
Keyway	Single
LED Indicator	None
Left Trunk Connector	Mini-Change
Left Trunk Gender	Male
Leg 1 Length	N/A

Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	TPE
Material - Coupling Nut	Zinc Die-Cast
Net Weight	158.757/g
Poles	5
Right Trunk Connector	Mini-Change
Right Trunk Gender	Female
Temperature Range - Operating	-20° to +80°C

This document was generated on Jun 02, 2026