HellermannTyton

Specification Sheet

Part Number: RB8L4

Product Image

Simple snap-in design allows for quick and easy installation or removal of cables.
Rubber based adhesive allows for a permanent bond to most surfaces.

RB Adhesive Cable Clamp, 0.32" Max. Bundle Dia, PA66, Natural, 200/pkg

Article Number	151-13608
Type	RB8
Color	Natural (NA)
Quantity Per	bag
Product Description	The RB Adhesive cable clamps are designed with an easy snap-in feature allowing simple installation or removal of cables, pipes or hoses. The rubber based adhesive allows for a permanent bond to most surfaces.
Short Description	RB Adhesive Cable Clamp, 0.32" Max. Bundle Dia, PA66, Natural, 200/pkg
Global Part Name	RB8-PA66-NA

Downloaded from Arrow.com.

Length L (Imperial)	0.98
Length L (Metric)	25.0
Fixation Method	Pasting / Stick
Variant	Closed
Width W (Imperial)	1.0
Width W (Metric)	25.0
Bundle Diameter Max (Imperial)	0.31
Bundle Diameter Max (Metric)	8.0
Height H (Imperial)	0.45
Height H (Metric)	11.5
Nominal Diameter (Imperial)	0.31
Nominal Diameter (Metric)	8.0
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66

Downloaded from Arrow.com.

Adhesive	Synthetic rubber with base of polyethylene foam
Flammability	UL 94 V-2 (excluding adhesive)
UV Resistant (Yes/No)	No
Adhesive Operating Temperature	-40°F to +140°F (-40°C to +60°C)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes

Package Quantity (Imperial)	200
Package Quantity (Metric)	200
Customs Number	3926909988

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.