Data sheet

STB 35 IH/SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



Current and voltage transformer wiring
Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

Version	Socket (terminal), Plug-in depth: 8 mm, Depth: 37.5 mm
Order No.	0388500000
Type	STB 35 IH/SW
GTIN (EAN)	4008190089726
Qty.	50 items

Downloaded from Arrow.com.

Data sheet

STB 35 IH/SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	37.5 mm	Depth (inches)	1.4764 inch
Width	7.2 mm	Width (inches)	0.2835 inch
Net weight	2.36 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea

Material data

Basic material	PA 66	Colour	black
UL 94 flammability rating	V-2		

System specifications

Version	For the mounting rails

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

Dimensions

Plug-in depth	8 mm

General

Installation advice	Direct mounting

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		

Downloaded from Arrow.com.