

626897 - 1 Product Details

No Image Available

626897 - 1



[Active](#)

Econoseal J Series [Mark II (+)]

[RoHS Compliant](#) [\(Statement of Compliance\)](#)

Product Highlights:

- ? Mounting Clip
- ? Nylon Body Material
- ? Panel Thickness = .56 - 5.11 mm
- ? Color = Natural

[View all Features](#)

Quick Links

[Check Pricing & Availability](#)  
[Search for Tooling](#)  
[Product Feature Selector](#)  
[Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [Christmas Tree](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? [AMP SEALED CONNECTORS](#) (PDF, English)

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [3D Model](#) (STEP, Version D)
- ? [3D Model](#) (IGES, Version D)
- ? [2D Drawing](#) (DXF, Version D)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Additional Product Images:

- ? [Panel Mount Cutout Dimensions](#)

Related Products:

- ? [Tooling](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Mounting Clip
- ? Body Material = Nylon
- ? Panel Thickness (mm [in]) = 0.56 – 5.11 [0.022 – 0.201]
- ? Color = Natural

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- ? GET 0.64 Connector System = No
- ? Brand = AMP