



Part Number : [1301430099](#)

Product Description : Super-Safeway Cordset 12 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA 5-15, 125V

Series Number : 130143

Status : Active

Product Category : Wiring Devices

Engineering Number : 1447B123



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not saleable
China RoHS	Not saleable
EU ELV	Not saleable
Low-Halogen Status	Not saleable
REACH SVHC	Not saleable
EU RoHS	Not saleable

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130143
Description	Super-Safeway Cordset 12 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA 5-15, 125V
IP Rating	N/A
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Specialty	N/A
Type	Cordset
UPC	78678862984

Agency

CSA	LR6837
UL	E38085

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Type	12/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	15.24m (50.0')
Lighted Connector	No
Locking Blade	No
Net Weight	9801.625/g
Poles	2-pole/3-wire

Receptacle Type	Single
-----------------	--------

This document was generated on Sep 18, 2025