

Part number

# CK 03 IA



Angled Bulkhead mounting housing, CK series, with 1 lever without cable entry, size "21.21", white colour

## Product description

|                      |                                  |
|----------------------|----------------------------------|
| <b>Product type</b>  | Angled bulkhead mounting housing |
| <b>Series</b>        | CK                               |
| <b>Closing type</b>  | With 1 lever                     |
| <b>Size</b>          | Size "21.21"                     |
| <b>Cable entry</b>   | Without cable entry              |
| <b>Specification</b> | White colour                     |

## Technical data

|                                |                                       |
|--------------------------------|---------------------------------------|
| <b>IP degree of protection</b> | IP44 - IP66 / IP67 / IP69 with CKR 65 |
|--------------------------------|---------------------------------------|

## Further technical details

|   |                |
|---|----------------|
| <b>Weight</b>                                 | 12,85 g        |
| <b>Operating temperature range (min, max)</b> | -40°C...+125°C |

## Material properties

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Other materials</b>       | Lever: Polyamide (PA)<br>Gasket: TPE |
| <b>Colour</b>                | RAL 7035 grey                        |
| <b>RoHs conformity</b>       | Compliant                            |
| <b>China RoHs - EFUP</b>     | E                                    |
| <b>REACH SVHC substances</b> | No                                   |

## Approvals / Standards

|            |       |
|------------|-------|
| <b>UL</b>  | ECBT2 |
| <b>cUL</b> | ECBT8 |

## General ordering information

|                   |               |
|-------------------|---------------|
| <b>EAN13 code</b> | 8015747026277 |
| <b>eCl@ss 8.1</b> | 27440202      |
| <b>ETIM 7.0</b>   | EC000437      |

## Packaging Information

|                                  |                       |
|----------------------------------|-----------------------|
| <b>Packaging length</b>          | 360,00 mm             |
| <b>Packaging height</b>          | 165,00 mm             |
| <b>Packaging width</b>           | 315,00 mm             |
| <b>Packaging weight</b>          | 1,70 kg               |
| <b>Packaging volume</b>          | 18,71 dm <sup>3</sup> |
| <b>Packaging description</b>     | Carton box            |
| <b>Packaging quantity</b>        | 100 Pcs               |
| <b>Packaging EAN code</b>        | 8015747026284         |
| <b>Sub-packaging weight</b>      | 0,17 kg               |
| <b>Sub-packaging description</b> | Plastic bag           |
| <b>Sub-packaging quantity</b>    | 10 Pcs                |
| <b>Sub-packaging EAN barcode</b> | 8015747026291         |

Part number



# CK 03 IA

Catalogue drawings



Catalogue drawings



---

## Notes

Dimensions shown in mm are not binding and may be changed without notice.

---