

Representative Image

Catalog No. TY29MX

Description: CABLE TIE 120LB 30IN UV BLACK NYLON

UPC No 786210830681

Home > Wire & Cable Management > Ty-Rap > Cable ties

High Performance Cable Tie, Black Color Nylon 6.6, Weather and Ultraviolet Resistant, Length of 762mm (30 Inches) for Bundle Diameter up to 229mm (9.02 Inches), Width of 6.9mm (0.27 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F)

Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	Black
Lock Mechanism	Stainless Steel Barb
Tensile Strength	120 pounds , 534 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405

Dimensions

Width	0.27 in , 6.9 mm
Length	30.3 in , 770 mm
Thickness	0.06 in , 1.5 mm
Bundle Diameter	Max 9.02 in , Max 229 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

Downloaded from Arrow.com.

ETIM	EC000046 Cable tie
Band width	0.27 inch
Band width	6.9 mm
Length belt/tape/tie	770 mm
Length belt/tape/tie	30.3 inch
Tie thickness	0.06 inch
Tie thickness	1.5 mm
Max. bundle diameter	229 mm
Max. bundle diameter	9.02 inch
Min. holding force	540 N
Operation temperature	-60-+85 °C
Operation temperature	-76-+185 °F
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	Y
UL approval	Y
Inflammability class of insulation material acc. with UL94	Other

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	2884	441406	N/A	1349334_2014-11-06	N/A
UL	E49405	N/A	ZODZ	N/A	N/A

Downloaded from Arrow.com.