Product Line

- DeepTronica
- Single Pair Ethernet
- ZConnect
- Ceres
- X-Lok
  - Accessory
  - Middle Size
  - Mini Size
  - Large Size
  - Standard Size
- M Series
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub





AD-04BFFM-QL8D02

Operating Temperature: -20°C ~ +80°C
Transmission Speed: N/A
Shielded: Plastic, Non-shielded
Jacket Material: PVC
Certificate: UL2238, UL50e

You must login first for view the price

Quantity − 1 +

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type | Search


X-Lok, Accessory,...
AB-AD-040404-...
-20°C ~ +85°C
− 0 +


X-Lok, Accessory,...
AB-AD-040404-...
-20°C ~ +85°C
− 0 +


X-Lok, Mini Size,...
AB-AD04ML-ADFL...
-20°C ~ +80°C
− 0 +


X-Lok, Mini Size,...
AB-AD04ML-ADFL...
-20°C ~ +80°C
− 0 +


X-Lok, Mini Size,...
AB-AD04ML-ADFL...
-20°C ~ +80°C
− 0 +


X-Lok, Mini Size,...
AB-AD04ML-ADFL...
-20°C ~ +80°C
− 0 +

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current **5A**	Connector Type **Overmolded**
Shielded **Plastic, Non-shielded**	No. of Contacts **04**
Connector Gender **Female**	Backshell **Straight**
Mating Style **Push Lock**	IP Rating **IP68**
Assembly Style **N/A**	

More Options

People Also Bought


AD-04BFFM-QL8D02


DD-14RFFS-RS8C50


AB-BB03BR-BBBR-...


HDB-44AMMM-...


CC-02BMMA-QL8SNP

Downloaded from Arrow.com.