



Part Number : [2159131006](#)

Product Description : Mini-Fit Max Receptacle Housing, Single Row, UL 94V-0, 6 Circuits, Glow-Wire Capable, Black

Series Number : 215913

Status : Active

Product Category : Connector Housings



Documents and Resources

Drawings

[2159131006_sd.pdf](#)

[2125140001-PK-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications


[2125150001-AS-000.pdf](#)

[2125150000-PS-000.pdf](#)

[2125150000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	215913
Description	Mini-Fit Max Receptacle Housing, Single Row, UL 94V-0, 6 Circuits, Glow-Wire Capable, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	Mini-Fit Max
UPC	195842607958

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	6
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes

Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.707/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Fit Max Vertical Single Row Headers	<u>215915</u>
Mini-Fit Max Right-Angle Single Row Through Hole Headers	<u>220924</u>
Mini-Fit Max Vertical Single Row Headers	<u>224491</u>
Mini-Fit Max Right-Angle Single Row Headers	<u>224900</u>

Use with Part(s)

Description	Part Number
Mini-Fit Max Female Crimp Terminals	<u>212515</u>
Mini-Fit Max Terminal Position Assurance (TPA) Retainers	<u>212516</u>

This document was generated on Jan 29, 2026