

[Products](#)[Customize Your Parts](#)[Industries Solutions](#)[Search](#)[News & Events](#)[First Time?](#)[Home](#) / [Products](#) / [M Series](#) / [M12 \(A\)](#)

Product Line

[Single Pair Ethernet](#) >[ZConnect](#) >[Ceres](#) >[X-Lok](#) >[M Series](#) >[Accessory](#)[M5](#)[Guided M8](#)[M8](#)[M10.5](#)[M12 \(A\)](#)[M12 \(B\)](#)[M12 \(D\)](#)[M12 \(I\)](#)[M12 \(K\)](#)[M12 \(L\)](#)[M12 \(S\)](#)[M12 \(T\)](#)[M12 \(V\)](#)[M23](#)[FLOS & FLOS+](#) >[Power](#) >[RBL](#) >[HS-Lok](#) >[NMEA 2000](#) >[Heavy Duty Shielded](#) >[RJ](#) >[USB](#) >[SSL](#) >[HDMI](#) >[DVI](#) >[Fiber Optic](#) >[RF](#) >[Cable Joiner](#) >[Cable Gland](#) >[Pressure Relief Vent](#) >[LED Light Guide](#) >[D-Sub](#) >

M12A-12PMMS-SF8C20

Operating Temperature: -20°C ~ +85°C

Transmission Speed: N/A

Shielded: Metal, Non-shielded

Jacket Material: PVC

Certificate: UL1977, UL2238, UL1863

You must login first to view the price

Quantity

- 1 +

 Add to Cart

 Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search



M Series, Accessory,...
CAP-WBDMQPC1
-20°C ~ +80°C



M Series, Accessory,...
CAP-WBDMSMA2
-40°C ~ +105°C



M Series, Accessory,...
CAP-WBDMSPB2
-40°C ~ +105°C



M Series, Accessory,...
IA-A12F-A12F-0000-01
-20°C ~ +85°C



Add to Cart



Inquiry

Specifications	Download / CAD
Nominal Current 1.5A	Connector Type Receptacle With Wires
Shielded Metal, Non-shielded	No. of Contacts 12
Connector Gender Male	Backshell Hexagonal
Mating Style Screw Thread	IP Rating IPX8
Assembly Style Solder	
 More Options	

People Also Bought