



Part Number : [2240415002](#)

Product Description : Micro-One Female Crimp Terminal, 2.00mm Pitch, 0.10µm Gold (Au) Plating, 28-26 AWG, Reel

Series Number : 224041

Status : Active

Product Category : Crimp Terminals



Documents and Resources

Drawings

[2240415002_sd.pdf](#)

[2240419200-SPK-200.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[2059790000-AS-000.pdf](#)

[2059790000-PS-002.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	224041
Description	Micro-One Female Crimp Terminal, 2.00mm Pitch, 0.10µm Gold (Au) Plating, 28-26 AWG, Reel
Application	Signal, Wire-to-Board
Product Name	Micro-One
UPC	196823621406

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold

Net Weight	33.790/mg
Packaging Type	Reel
Plating min - Mating	0.100µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.88-1.30mm
Wire Size (AWG)	26, 28
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Micro-One Wire-to-Board Receptacle Housings	<u>205979</u>
Micro-One Single Row Receptacle Housings	<u>212724</u>
MicroClasp Dual Row Receptacle Housings	<u>51353</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for MicroClasp Receptacle Crimp Terminals, 28-22 AWG, UL1007 Wires	<u>2133090400</u>
FineAdjust Applicator for Micro-One Wire-to-Board Terminal, 28-26 AWG (UL1007) Wires	<u>2037026000</u>

Japan

Description	Part Number
S-1 Applicator for 2.00mm Pitch Micro-One Receptacle Terminal, 28-26 AWG	<u>2063233710</u>

This document was generated on Apr 14, 2026