Your Expert Partner for **Human Machine Interfaces**

Actuator

61-
0010.02



https://www.eao.com/component/61-0010.02/en/a...

Downloaded from Arrow.com.

Your product:



61-0010.02
Actuator

FRONT

Front dimension:	Ø 18 mm
Front form:	Round
Front bezel colour:	Black
Front bezel material:	Plastic

MOUNTING

Mounting cut-out:	Ø 16 mm
Mounting type:	Panel mounting

MECHANICAL CHARACTERISTICS

Terminal:	Plug-in terminal, 2.8 x 0.5 mm
Tightening torque:	Max. 0.5 Nm
Weight:	0.007 kg

AMBIENT CONDITION

IP Protection:	IP40 rear side, according to EN IEC 60529, IP67 front side, according to EN IEC 60529
Operating temperature:	– 25 °C ... + 55 °C
Storage temperature:	– 40 °C ... + 85 °C

CERTIFICATE


Downloaded from Arrow.com.

REACH:	REACH compliant
RoHS:	RoHS compliant


OTHER

Short Description:	Actuator, Ø 16 mm, Ø 18 mm, Round, Black, Plastic, Plug-in terminal, 2.8 x 0.5 mm
Internal size:	Ø 15,8 mm
Housing colour:	Black
Housing material:	Plastic, according to UL 94 V0, self-extinguishing

Wiring diagrams:




Mounting cut-outs:



Dimension drawings:

Downloaded from Arrow.com.



Downloaded from Arrow.com.