HellermannTyton

Technical data sheet

Article number:
561-00644 WIC0-4



Product Group	Pre-printed cable markers
Product Family	WIC, snap on
Material	Polyamide 6.6 (PA66)
Colour	Yellow (YE)

Application Tool	WIC Tool
Bundle Ø max.	2.20 mm
Bundle Ø min.	0.80 mm
Flammability	UL 94 V0
Height (H)	5.50 mm
Length (L)	3.00 mm
Marking Text	4
Operating Temperature	-40 °C to +85 °C
Package Content	1000 pcs.
Package Content packed in	box
Print Method	inkjet print
Specifications	EN 60062, IEC 304
Width (W)	5.00 mm
Wire Size Range (mm²)	0.15-0.75 mm²

HF RoHS

created on 22. May 2026, 6:30 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.