

Microwave Components/Modules > Antennas > Chip Antennas

How to check EU RoHS Compliance of Our Products is [here](#).

Product Lifecycle Stage	in Production
Recommended Rank	Preferred

Specifications

Global Part Number	ANCG12G44SAA148RD1
Previous Part Number	
Fo	2442MHz
Bandwidth	84MHz
Applications	WLAN/BT
VSWR (max.)	4.0
Impedance	50ohm
Power Capacity	1W
Min. of Operating Temperature	-40°C
Max. of Operating Temperature	+85°C
Use form	On GND
Notes	Mirrored pattern of ANCG12G44SAA145

Details

-  [Part Numbering](#)
-  [Appearance](#)
-  [Dimensions](#)
-  [Land_Pattern](#)
-  [Return_Loss](#)
-  [Directivity](#)
-  [Dimensions_of_Taping](#)
-  [Notice](#)

Minimum Quantity

180mm Paper Tape	
180mm Embossed Tape	
330mm Paper Tape	
330mm Embossed Tape	1000
Bulk Case	
Bulk(Bag)	
Ammo Pack	
320Reel	
Magazine	
Box	

Please approve our product specifications or to transact the approval sheet for product specifications before ordering.

Please read rating and !Cautions first.

Product specifications in this catalog are as of November 2012

Please make sure to read the Murata's [Product Policy](#) ,too.

All products and company names herein are trademarks or registered trademarks of their respective owners.