

Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies

193888-E

ACTIVE

68 Positions, .1 m [.33 ft], Red Cable, 30 AWG, .05 mm², Ribbon Cable, Socket Housing, Socket Housing, VW-1



ERNI | ERNI SMC
TE Internal #: **193888-E**
TE Internal Description: **IDCCS SMC 1,27 68 * AU AUI 100 PV C**

Cable Assembly (End A) : **Socket Housing**
Cable Assembly (End B) : **Socket Housing**
Wire Size (AWG): **30**
Wire Size (mm²): **.05**
Shielded : **No**

[Add to List](#) | [Similar Products](#) | [Digital Datasheet](#)

Compatible Parts & Tooling

SHOP OUR DISTRIBUTORS

North America	See all price breaks
Distributor	110,000Buy

We are here to help!
Get in touch with our product experts.

CHAT WITH US

EMAIL US

CALL US

Documents

Features

Product Compliance

CAD Files

- Download ECAD Model File
- Request Free CAD Models
- Download the free Library Loader to convert this file to your ECAD Tool.
[Learn more about the ECAD Model.](#)
- 3D PDF
- 3D_CVM_CVM_193888-E_C.pdf
- 3D
- Customer View Model
- ENG_CVM_CVM_193888-E_C.2d_dxf.zip
- English
- ENG_CVM_CVM_193888-E_C.3d_igs.zip
- English
- ENG_CVM_CVM_193888-E_C.3d_stp.zip
- English

Datasheets & Catalog Pages

- Datasheet - ERNI SMC 1.27mm Connectors
- ENG_DS_erni-smc-1.27mm-connectors-ds_2401.pdf
- English
- Datasheet - ERNI SMC 1.27mm Connectors
- GER_DS_erni-smc-1.27mm-connectors-ds_2401.pdf
- German

REPORT PRODUCT DATA ERROR

Compatible Parts

All Compatible Parts (5)

Associated Parts (1)

Mating parts (4)

Filter By Specification

MATING
154766-E
PCB Mount Header, Right Angle, Board-to-Board, 68 Position, 1.27 mm [.05 in]...

From: \$8.485
In-Stock

[VIEW PRODUCT](#)

ASSOCIATED
168304-E
16 Positions, .3 m [.98 ft], Gray / Red Cable, 30 AWG, .05 mm², Ribbon Cable, Socket...

Non-Stocked

[VIEW PRODUCT](#)

MATING
234209-E
PCB Mount Header, Vertical, Board-to-Board, 68 Position, 1.27 mm [.05 in] Centerline...

From: \$4.809
In-Stock

[VIEW PRODUCT](#)

MATING
244839-E
PCB Mount Header, Vertical, Board-to-Board, 68 Position, 1.27 mm [.05 in] Centerline...

From: \$4.046
In-Stock

[VIEW PRODUCT](#)

MATING
244857-E
PCB Mount Header, Vertical, Board-to-Board, 68 Position, 1.27 mm [.05 in] Centerline...

From: \$3.522
In-Stock

[VIEW PRODUCT](#)

Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

PLUGGABLE I/O CABLE ASSEMBLIES

193888-E
68 Positions, .1 m [.33 ft], Red Cable, 30 AWG, .05 mm², Ribbon Cable...

In-Stock

Cable Assembly (End A) : **Socket Housing**
Cable Assembly (End B) : **Socket Housing**
Wire Size : **30 AWG**
Wire Size : **.05 mm²**
Shielded : **No**

TOP RESULTS

PLUGGABLE I/O CABLE ASSEMBLIES

168301-E
16 Positions, .1 m [.33 ft], Red Cable, 30 AWG, .05 mm², Ribbon Cable...

Non-Stocked

Cable Assembly (End A) : **Socket Housing**
Cable Assembly (End B) : **Socket Housing**
Wire Size : **30 AWG**
Wire Size : **.05 mm²**
Shielded : **No**

PLUGGABLE I/O CABLE ASSEMBLIES

168312-E
20 Positions, .1 m [.33 ft], Red Cable, 30 AWG, .05 mm², Ribbon Cable...

Non-Stocked

Cable Assembly (End A) : **Socket Housing**
Cable Assembly (End B) : **Socket Housing**
Wire Size : **30 AWG**
Wire Size : **.05 mm²**
Shielded : **No**

PLUGGABLE I/O CABLE ASSEMBLIES

168338-E
40 Positions, .1 m [.33 ft], Red Cable, 30 AWG, .05 mm², Ribbon Cable...

Non-Stocked

Cable Assembly (End A) : **Socket Housing**
Cable Assembly (End B) : **Socket Housing**
Wire Size : **30 AWG**
Wire Size : **.05 mm²**
Shielded : **No**

Customers Also Bought

TE Part #: **966066-5**
Ferrule, 26 AWG Wire Size, .12 ~ .15 mm² Wire Size...

\$0.136 per unit
Inventory: In-Stock

[Add To Cart](#)

TE Part #: **62194-2**
Pigtail Splice / Thru Splice, 24 ~ 19 AWG Wire Size, .2 ~...

\$0.116 per unit
Inventory: In-Stock

[Add To Cart](#)

TE Part #: **2-160967-1**
Standard, Bag, 18.5 lbf Tensile Strength, 82...

[View Product](#)

TE Part #: **15NK516151R0000**
Ground, Screw Clamp Terminal Block, Green &...

[View Product](#)

TE Part #: **214013-E**
PCB Mount Header, Right Angle, Cable-to-Board, 6...

[View Product](#)

TE Par

PCB M

Angle,

[View Product](#)

Also in the Series | ERNI SMC

Board-In Connectors (6)

Connector Adapters & Connector Savers (45)

PCB Headers & Receptacles (81)

Pluggable I/O Cable Assemblies (27)

Wire-to-Board Connector Assemblies & Housings (5)

Contact Our Team – 24/7 Support

+1 800 522 6752

Chat

Submit Feedback

See Support Details

Connect With Us



Access Partner Information

Distributors

Suppliers

Supplier Diversity

Get Answers Now

Authorized Distributors & Resellers

Product FAQs

Samples FAQs

TE Store FAQs

Terms and Conditions of Sale

Samples Terms and Conditions

Select Your Preferences

Language

English (EN)

Ship to

United States (\$USD)