



+ RELAYS, CONTACTORS & SWITCHES

TO-5/.100 GRID



✓ Active

3D PDF

After your visit, would you be willing to provide some quick feedback?

(It will only take a minute)

Yes

No Thanks

powered by opinionlab.

Transistor Driver Without



CAD Files

3D PDF

PDF
3D

Customer View Model

2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP
English

Customer View Model

3D_STP.ZIP
English

Catalog Pages/Data Sheets

5-1773450-5_sec1_MGS

PDF
English



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	MOSFET Driver	Without
	Enclosure Type	Hermetically Sealed
	Product Type	Relay
	Relay Type	Military/Aerospace High Performance
Configuration Features	Transistor Driver	Without
Electrical Characteristics	Input Voltage (VDC)	26.5
	Coil Suppression Diode	With
	Coil Voltage (VDC)	26.5
	Coil Resistance (Ω)	3200
	Coil Power Rating (DC) (mW)	219
	Coil Polarity Protection Diode	With
	Actuating System	DC
	Vibration	30G's, 10 – 3000Hz
	Coil Power Measurement	Milliwatts
	Coil Magnetic System	Non-Polarized, Monostable
Contact Features	Shock	75G's, 6ms
	Contact Arrangement	2 Form C, DPDT, 2 C/O
	Contact Current Rating (A)	1
	Pin Configuration	.175" Diameter Mounting Pad
Termination Features	Contact Current Class	Low Level – 1 A
	Termination Type	Long Leads
Mechanical Attachment	Mounting Type	Printed Circuit Board
Usage Conditions	Operating Temperature Range (°C)	-65 – 125
Product Compliance	Statement of Compliance PDF	
	VIEW ALL PRODUCT COMPLIANCE	

