



**Part Number :** [459842163](#)

**Product Description :** EXTreme LPHPower Receptacle Header, Right-Angle, 2 Power Contacts, 32 Signal Contacts, Select Gold (Au) Plating, for 1.57mm Thick PC Board

**Series Number :** 45984

**Status :** Active

**Product Category :** Board-to-Board Connectors



---

## Documents and Resources

### Drawings

[459842163 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)


### Specifications

[PS-45984-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Compliant with Exemption 44; 34; 33   |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Not Contained per D(2025)7771-DC (04 Feb 2026)  |
| EU RoHS            | Compliant per EU 2015/863   |

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

|                |  |
|----------------|--|
| Status         | Active   |
| Category       | Board-to-Board Connectors  |
| Series         | 45984  |
| Description    | EXTreme LPHPower Receptacle Header, Right-Angle, 2 Power Contacts, 32 Signal Contacts, Select Gold (Au) Plating, for 1.57mm Thick PC Board |
| Application    | Board-to-Board, Power, Signal  |
| Component Type | Receptacle   |
| Product Name   | EXTreme LPHPower   |
| UPC            | 195842345317   |

### Agency

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

### Electrical

|                               |   |
|-------------------------------|---|
| Current - Maximum per Contact | 30.0A                                     |
| Grounding to PCB              | No  |
| Voltage - Maximum             | 250V AC (RMS)/DC (Power), 30V DC (Signal) |

## Physical

|                                |                                |
|--------------------------------|--------------------------------|
| Circuits (Loaded)              | 34                             |
| Circuits (maximum)             | 34                             |
| Color - Resin                  | Black                          |
| Durability (mating cycles max) | 250                            |
| Flammability                   | 94V-0                          |
| Glow-Wire Capable              | No                             |
| Guide to Mating Part           | No                             |
| Keying to Mating Part          | No                             |
| Lock to Mating Part            | No                             |
| Material - Metal               | Copper Alloy                   |
| Material - Plating Mating      | Gold                           |
| Material - Plating Termination | Tin                            |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 5.059/g                        |
| Number of Rows                 | 2                              |
| Orientation                    | Right Angle                    |
| Packaging Type                 | Tray                           |
| PCB Locator                    | No                             |
| PCB Retention                  | No                             |
| PCB Thickness - Recommended    | 1.57mm                         |
| PC Tail Length                 | 2.90mm                         |
| Pitch - Mating Interface       | 12.00mm, 1.27mm                |
| Pitch - Termination Interface  | 2.00mm, 2.50mm, 1.27mm         |
| Plating min - Mating           | 0.762µm                        |
| Plating min - Termination      | 3.810µm                        |
| Polarized to Mating Part       | Yes                            |
| Polarized to PCB               | Yes                            |
| (p)ower-(s)ignal Configuration | 2p - 32s                       |
| Stackable                      | No                             |
| Temperature Range - Operating  | -40° to +105°C                 |
| Termination Interface Style    | Through Hole                   |

---

## Mates With / Use With

## Mates with Part(s)

| Description                        | Part Number      |
|------------------------------------|------------------|
| EXTreme LPHPower Right-Angle Plugs | <u>45985</u>     |
| Mates With                         | 1.57mm Card Edge |

---

This document was generated on May 08, 2026