



Part Number : 1300940358

Product Description : Standard Duty Support Grip, Locking Bale, Split Lace, Single Weave, Cable Diameter 31.75-37.85mm (1.250-1.490"), Approximate Break Strength 870.90kg (1920 lbs)



Series Number : 130094

Status : Active

Product Category : Cable Grips

Engineering Number : 35229

Documents & Resources

Drawings

[PK-130227-004-001.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of ComplianceAdditional Product Compliance Information**Part Details****General**

Status	Active
Category	Cable Grips
Series	130094
Description	Standard Duty Support Grip, Locking Bale, Split Lace, Single Weave, Cable Diameter 31.75-37.85mm (1.250-1.490"), Approximate Break Strength 870.90kg (1920 lbs)
Product Name	Standard Duty
Type	Support Grip
UPC	78678835229

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	870.90kg (1920 lbs)
Bale Length	0.457m (18.00")
Body Style	Straight
Cable Diameter	31.75-37.85mm (1.250-1.490")
Color - Grommet	N/A
Eye Type	Locking Bale
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.406m (16.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

This document was generated on Sep 22, 2025