

Low-Profile VGA High-Resolution RGB Coaxial Cable (HD15 M/M), 50 ft. (15.24 m)

MODEL NUMBER: P502-050-SM



Allows a high-resolution connection between your VGA-enabled computer and monitor up to 50 ft. apart with no ghosting.

Description

The P502-050-SM VGA Coaxial High-Resolution Monitor Cable (M/M) allows you to connect your VGA-enabled computer and monitor up to 50-ft. (15.24 m) apart. Constructed from mini-coaxial (RGB) and paired video wire, it supports video resolutions up to 2048 x 1536, including 1080p, with no ghosting. It's more than 40% smaller in diameter than standard VGA cables, which increases airflow in tight spaces and makes it easier to install around corners.

Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded HD15 male connectors with gold-plated contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

Features

Allows Connection Between VGA-Enabled Computer and Monitor Up to 50-ft. (15.24 m)

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded HD15 male connectors and gold-plated contacts provide maximum conductivity and minimize data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

Special Slim Design

- More than 40% smaller in diameter than standard VGA cable
- Increases airflow in tight spaces
- Increased flexibility for installing around corners

Specifications

Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated contacts for maximum conductivity
- Over 40% slimmer than standard VGA cables

System Requirements

- Display device with HD15 input
- Computer with HD15 output

Package Includes

- P502-050-SM Low-Profile VGA Coaxial High-Resolution Monitor Cable (M/M), 50-ft. (15.24 m)



Powering Business Worldwide

TRIPP LITE
SERIES

OVERVIEW	
UPC Code	037332185945
Product Type	Passive Cable
Technology	Coax; VGA/SVGA
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	HD15 (MALE) - LOW PROFILE
Side B - Connector 1	HD15 (MALE) - LOW PROFILE
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	50
Cable Length (m)	15.24
Cable Length (in.)	600
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Weight (lbs.)	0.96
Shipping Weight (kg)	0.44
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.