Part Number : 190740024
Product Description : Krimptite Steel Star Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier
Series Number : 19074
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : SRB-S-129-08T



Documents and Resources

Drawings

190740024_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19074
Description	Krimptite Steel Star Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite
Style	Ring
Type	Ring Terminal
UPC	800753079106

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.540/g
Packaging Type	Adhesive Tape on Reel
Stud Size	8 (M4)
Termination Interface Style	Crimp or Compression

Downloaded from Arrow.com.

Wire Size (AWG)	14, 16

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	190270184

Downloaded from Arrow.com.