



Part Number : [1301070043](#)

Product Description : Watertite Wet Location 26W
Fluorescent Stringlight 12/3 SOOW 5 Lamps Lead,
19.81m (65.0') Cord Length

Series Number : 130107

Status : Active

Product Category : Lamps and Lights

Engineering Number : 387510A



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130107
Description	Watertite Wet Location 26W Fluorescent Stringlight 12/3 SOOW 5 Lamps Lead, 19.81m (65.0') Cord Length
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Name	Watertite
Type	String Lights
UPC	78678834337

Electrical

Lamp Wattage - Maximum	26W
Lumens	1800
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Fluorescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	12/3 SOOW
Depth	59.70m (2.350")
Duty	Wet Location
Guard Included	No
Guard Type	Steel
Height	445.01mm (17.520")
Lamp Type	PL-C 26/41/4P
Length	19.81m (65.0')
Material - Globe	Butyrate
Material - Guard	N/A

Mounting Style	Stringer
Outlet	None
Packaging Type	Carton
Socket Construction	Rubber Molded

This document was generated on Sep 16, 2025