Part Number : 1300280087
Product Description : Micro-Change (M12) Double-Ended Cordset, 5 Poles, Male (Straight) to Female (90°), 22 AWG, Gray DeviceNet Thin Stranded Cable, 2.0m (6.56') Length
Series Number : 130028
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : DND32A-M020



Documents & Resources

Drawings
1300280087_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130028
Description	Micro-Change (M12) Double-Ended Cordset, 5 Poles, Male (Straight) to Female (90°), 22 AWG, Gray DeviceNet Thin Stranded Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	DeviceNet,Micro-Change (M12)
Type	Double Ended
UPC	78678838025

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	7.24mm (.285")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Gray
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single

Downloaded from Arrow.com.

LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Die-Cast
Material - O-Ring	Nitrile Rubber
Material - Plating Mating	Gold
Net Weight	169.189/g
Orientation	90° to Straight
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Thin (Drop)
Wire Size (AWG)	22

This document was generated on Mar 08, 2025

Downloaded from Arrow.com.