

Optical Storage

iHAS124-04



BLU-RAY

DVD RW

Internal

External Slim

DVD ROM

SSD



iHAS124-04

Specification

Firmware

Technology Center

Specification

EZ-DUB

SmartWrite

Blu-ray

Super AllWrite

SmartErase

DVD Family

Write

DVD+R

24X*

DVD-R

24X*

DVD+R DL

8X

DVD-R DL

8X

ReWrite

DVD+RW

8X

DVD-RW

6X

Read

DVD+ROM

16X

Random Access time

160ms

Write

CD-R

48X

ReWrite

CD-RW

24X

Read

CD-ROM

48X

Random Access time

140ms

CD Family

Buffer Size

0.75MB (MAX)

PC Required

1GHz or faster CPU recommended.
Windows 8 requires SSE2, PAE and NX-bit Support.
1GB RAM and 16GB free disk space required under 32-bit OS (2GB RAM and 20GB space under 64-bit OS) for creating DVD Disc.
Available SATA port required.

Compatibility

DOS 6.xx, Windows 8 / Windows 7 / XP / 2003 / Vista and Linux operating system

Environment

Compatibility

Operating 5°C to 50°C; Relative Humidity 20% to 80%

Non-Operating

-40°C to 65°C; Relative Humidity 5% to 90%

General

Dimension

146(W) x 41.3(H) x 170(D)

mm

Weight

< 0.9Kg

* in order to reach 24X only certain recommended high quality media can be used

<< Zurück - Weiter >>



Feedback Analytics