

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -



ALL RIGHTS RESERVED.

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	16JUN2015	DL	CW
	B	ECR-20-014876	16JUL2021	WQR	CW

4X M3 THREAD
4X M3 螺纹孔



4-Ø5.5



SCALE 2:5



TYPE 2: BODY + STAINLESS STEEL LOCKING
BOTTOM ENTRY
OTHER SPEC REFER TO TYPE 1



TYPE 1: BODY + STAINLESS STEEL LOCKING
SIDE ENTRY

TI440241121-000	TYPE 1	H24B-SGRS-PG21	PG21	-	-
TI440241125-000		H24B-SGRS-M25	M25	-	-
TI440241221-000		H24B-SGRS-2PG21	PG21	PG21	-
TI440241225-000		H24B-SGRS-2M25	M25	M25	-
TI440245225-000	TYPE 2	H24B-SGRS-T2M25	-	-	M25
ASSEMBLY PART NUMBER	TYPE	ASSEMBLY PART DESCRIPTION	IG1	IG2	IG3

NOTES:

1. TECHNICAL CHARACTERISTICS:
BODY MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE TREATMENT: POWDER-COATED, GRAY
DEGREE OF PROTECTION: IP65 (MATED)

注释:

1. 技术参数:
主体材料: 铝合金
表面处理: 粉末喷涂, 灰色
防护等级: IP65(配合)

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±
MATERIAL -	FINISH -

DWN DAVID LI 16JUN2015	CHK CHRIS WANG 16JUN2015
APVD XU XIANG 16JUN2015	PRODUCT SPEC 108-137013
APPLICATION SPEC 114-137013	WEIGHT -
CUSTOMER DRAWING	



TE Connectivity

NAME
H24B-SGR/SGRS-PG/M

SIZE A3	CAGE CODE -	DRAWING NO C-TI44024XXXXX00	RESTRICTED TO
------------	----------------	--------------------------------	---------------

SCALE 1:2	SHEET 1 OF 2	REV B
--------------	-----------------	----------

Printed on 20 Jul 2021 16:15 (China Standard Time) from TE343646

D

A

4

3

2

1

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20
© COPYRIGHT 20		BY -		ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D


C


B

A



TI440242121-000	TYPE 3	H24B-SGR-PG21	PG21	-	-	
TI440242125-000		H24B-SGR-M25	M25	-	-	
TI440242221-000		H24B-SGR-2PG21	PG21	PG21	-	
TI440242225-000		H24B-SGR-2M25	M25	M25	-	
TI440242521-000		H24B-SGR-M25/PG21	M25	PG21	-	
TI440242125-100	TYPE 4	H24B-SGR-M25	M25	-	-	SEAL FIXED BY GLUE
TI440242125-200	TYPE 5	H24B-SGR-M25	M25	-	-	NO SEAL PART
TI440242809-000	TYPE 6	H24B-SGR-8PG9	-	-	PG9	
ASSEMBLY PART NUMBER	TYPE	ASSEMBLY PART DESCRIPTION	IG1	IG2	IG4	REMARK
TABLE: TYPE DESCRIPTION						



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 16JUN2015		TE Connectivity						
		CHK CHRIS WANG 16JUN2015								
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		APVD XU XIANG 16JUN2015		NAME H24B-SGR/SGRS-PG/M				
				PRODUCT SPEC 108-137013						
				APPLICATION SPEC 114-137013						
				SIZE A3		CAGE CODE -	DRAWING NO C-TI44024XXXXX00	RESTRICTED TO		
				WEIGHT -						
MATERIAL - -		FINISH - -		CUSTOMER DRAWING				SCALE 1:2	SHEET 2 OF 2	REV B