Part Number : 847330004
Product Description : Sealed Industrial USB 3.0 Type A Receptacle-to-USB Type A Plug Dual-Ended Cordset, 0.81m Length
Series Number : 84733
Status : Active
Product Category : I/O Cable Assemblies



Documents and Resources

Drawings

847330004_sd.pdf

Specifications

PS-84733-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Imidazolidine-2-thione per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	I/O Cable Assemblies
Series	84733
Description	Sealed Industrial USB 3.0 Type A Receptacle-to-USB Type A Plug Dual-Ended Cordset, 0.81m Length
Assembly Configuration	Dual Ended Connectors
Comments	Fully shielded for EMI/RFI protection
Connector to Connector	USB Type A-to-A
Product Name	Industrial USB
UPC	887191633206

Electrical

Current - Maximum per Contact	1.0A
Impedance	Non-constant
Shielded	Yes
Shield Type	Full Shield
Voltage - Maximum	30V AC (RMS)

Physical

Cable Length	0.81m
Circuits (Loaded)	4
Circuits (maximum)	4

Downloaded from Arrow.com.

Color - Resin	Black
Gender	Female-Male
Material - Resin	PVC
Net Weight	21.910/g
Packaging Type	Bag
Single Ended	No
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67, NEMA 6P
Wire/Cable Type	USB
Wire Size (AWG)	N/A

Downloaded from Arrow.com.