



Part Number : [391001802](#)
Product Description : 8.00mm Pitch, Beau Eurostyle
Two-Screw Terminal Strips, 2 Circuits
Series Number : 39100
Status : Active
Product Category : Terminal Blocks and Barrier
Strip
Engineering Number : M800-01-02-5-M1



Documents & Resources

Drawings

[391001802_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39100
Description	8.00mm Pitch, Beau Eurostyle Two-Screw Terminal Strips, 2 Circuits
Application	Wire-to-Wire
Component Type	One Piece
Keyword	Terminal Strip
Product Name	Eurostyle Two Screw
Type	Terminal Strips
UPC	78172545120

Electrical

Current - Maximum per Contact	20.0A
Voltage - Maximum	600V

Physical

Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	White
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Stainless Steel, Steel
Material - Resin	Nylon

Net Weight	5.380/g
Number of Rows	2
Orientation	Vertical
Panel Mount	Mounting Holes Between Circuit
Pitch - Mating Interface	8.00mm
Pitch - Termination Interface	8.00mm
Polarized to Mating Part	N/A
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Screw
Wire Size (AWG)	12, 14, 16, 18, 20, 22
Wire Size mm ²	0.33-3.31

This document was generated on Sep 17, 2025