

YSV10BOX, Uninsulated Splice For 12 - 10 AWG

By Burndy
Catalog # [YSV10BOX](#)

Uninsulated Splice For 12 - 10 AWG



Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper dept of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

Application

For All Heavy Duty Industrial And General Purpose Applications

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	12-10 AWG
Conductor - Copper Solid Size	12-10 AWG
Conductor - Copper Str Aircraft Size	<ul style="list-style-type: none"> • AN 12 • AN 10
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size

Configuration

Connector Type Seamless Butt Splice

Current

Voltage - Maximum 35000 V

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.21 in
Dimension - L Length Overall mm	19 mm
Package Height	0.000 in
Dimension - Strip Length inch	5/16 in
Dimension - Length Overall inch	0.75 in

General

Trade Name	HYLINK™
Sub Brand	HYLINK
Plated	Y
Feature - Barrel Style	Chamfered
Type	Splice
UPC 14 Digit GTIN	00781810543603
Material	Copper
Plating Type	Tin
UPC	781810543603

Logistics

Minimum Pack Quantity	50
Carton Quantity	600
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)