

BSCH001005051N3SCP

Search by : Part Number Characteristics Cross reference



MP

Multilayer-STD

Series Pdf

RoHSREACHCoC


ICP Report

Product detail	
Structure	Multilayer
L(mm) ±	1.0±0.10
W(mm) ±	0.5±0.1
T(mm) ±	0.5±0.1
Size Code (JIS/EIA)	1005/0402
Inductance(nH)	1.3
Unit	nH
Tolerance(±%)	0.3nH
Test Frequency(L)	100 MHz,200 mV
Q Min	8
Test Frequency(Q)	100 MHz,200 mV
SRF(MHz)Typ	9000
RDC(Ω)Max	0.1
Rated Current(mA)Max	300

Downloaded from Arrow.com.

Operating Temperature	−55℃～125℃(Including self - temperature rise)

Part Numbering | Dimensions | Packing | Recommended Pattern | Electrical Characteristics | S Parameter



Products

Power Inductor

EMI-Common Mode Choke

EMI-Bead

RF-Signal Inductor

RF-Passives/Antennas

LAN Transformer

Resistor & Current Sensor

Applications

Automotive

Industrial

Server/DataCenter

Communication

Mobile and Tablet

Computer/Laptop

Consumer

Design Tools

Simulation Tool

Product Search Engine

E-Catalogue

About Us

Corporate Overview

Corporate Milestones

Core Technology

Certificates & Awards

Quality and Social Responsibility

Downloaded from Arrow.com.

Investor

Financial Information

Corporate governance

Stakeholder Contacts

News

Media Center

New Products

Events

Product Notices

Contact Us

Contact Info

Contact Form

Join Chilisin

Terms of Use

Privacy policy

Sitemap

Inductor Resistor Powder

Copyrights © 2018. Chilisin. All rights reserved.

Downloaded from Arrow.com.