

Part Number : [191930094](#)

Product Description : VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Closed-Brazed Barrel, Stud Size 1/2" (M12), Carton

Series Number : 19193

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : C-301-12



Documents and Resources

Drawings


[191930094 sd.pdf](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Closed-Brazed Barrel, Stud Size 1/2" (M12), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800755049268

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	2.519/g
Packaging Type	Carton
Stud Size	1/2" (M12)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	5.76mm max.
Wire Size (AWG)	10, 12

Wire Size mm ²	4.00-6.00
---------------------------	-----------

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm ² - 0.5mm ²	<u>640030100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>

This document was generated on May 04, 2026