
VICOR CONFIDENTIAL


THIS DOCUMENT AND THE DATA DISCLOSED HEREIN OR HEREWITH IS NOT TO BE REPRODUCED, USED OR DISCLOSED IN WHOLE OR IN PART TO ANYONE WITHOUT THE PERMISSION OF VICOR CORP.


REV.	DESCRIPTION		DATE	APPROVED
1	RELEASED PER E0230307	PEI	07/11/02	JMR
2	REVISED PER E080070	SA	01/11/08	REJH
3	REVISED PER E091753	JS	09/29/09	REJH
4	REVISED PER E092276	JS	12/30/09	REJH
5	REVISED PER E120065	VSS	01/20/12	KUK
















DASH NO.	SOCKET BODY LENGTH	DIM "A"	DIM "B"	INPUT	OUTPUT	KIT#
-01	.100/2.54	.280/7.11	.280/7.11	18378	18388	18364
-02	.135/3.43	.315/8.00	.315/8.00	18379	18389	18365
-03	.160/4.06	.340/8.64	.340/8.64	21539	21543	21510

NOTE:
1. MATERIALS: INMATES: PPS RYTON 7
   SOCKETS: BE-CU #25, Au PLATED.
2. FULLY SEAT SOCKET INTO INMATE HEADER.
3. ROHS COMPLIANT PER CST-0001 LATEST REVISION.





DRAWN BY	DATE
Lap Nguyen	6/99

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE : INCH / [MM]

TOLERANCES ARE:
DECIMALS ANGLES
X.XX [X.X] ± ±0.01 [0.25] ±1°
X.XXX [X.XX] ± ±0.005 [0.127]

THIRD ANGLE PROJECTION

DO NOT SCALE DRAWING

VICOR SWD

DWG,VI-900
INMATE/SOCKET,BOB

SIZE	CAGE CODE	DWG NO	REV
D	67131	18480-XX	5

SCALE 4:1 SHEET 1 OF 1

Downloaded from Arrow.com.