

**Part Number :** [1300950200](#)

**Product Description :** Junior Duty Wire Mesh Pulling Grip, Single Weave, Flexible Eye, Mesh Length 0.254m (10.00"), Approximate Break Strength 1859.73kg (4100 lbs)

**Series Number :** 130095

**Status :** Active

**Product Category :** Cable Grips

**Engineering Part Number :** 35974



---

## Documents and Resources


### Drawings

[1300950200\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	Cable Grips
Series	130095
Description	Junior Duty Wire Mesh Pulling Grip, Single Weave, Flexible Eye, Mesh Length 0.254m (10.00"), Approximate Break Strength 1859.73kg (4100 lbs)
Product Name	Junior Duty
Type	Pulling Grip
UPC	78678835974

#### Agency

CSA	LR32159
-----	---------

#### Physical

Approximate Break Strength	1859.73kg (4100 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	19.05-25.15mm (.750-.990")
Color - Grommet	N/A
Eye Type	Flexible
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.254m (10.00")
Net Weight	86.754/g
Number of Holes	N/A
O-Ring	N/A

Thread Size	N/A
-------------	-----

---

This document was generated on Apr 27, 2026