






Z





Y



A-B
2:1

X Kontaktbelegung
contact loading





Referenzebene Tiefe
datum plane depth

09 25 130 6571	2	Au flash over PdNi over Ni
Bestell-Nr. part-no.	Anforderungsstufe nach IEC performance level acc. to IEC	Kontaktoberfläche contact plating

Z
10:1

Querschnitt der
Lötanschlüsse:
cross-section of
solder terminations:



All Dimensions in mm
Original Size DIN A 3

Techn. Character.

	Dat.	Name	Maßstab/Scale
Detail.	05.05.09	MR	1:1
Insp.	05.05.09	RA	2:1
Stand.			10:1

HARTING Electronics GmbH & Co. KG
D-32339 ESPELKAMP



Nicht tolerierte Maße/Free size tolerances
IEC 60603-2

Bauform 3C Messerleiste ohne Flansch
Einlöt, 30 pol.
type 3C male connector without flange
solder, 30 pol.

TB 09 25 130 x571

Blatt/ page

Sub.

35605		
Mod.	Dat.	Name