






PART NUMBER	PACK	HOOD SIZE
8655AMETIAI1K00ILF	KIT	09








NOTES: (FOR EVERY SIZES)
1- OPERATING TEMPERATURE: -40°C TO +120°C
2- INDIVIDUAL KITS SEALED IN PLASTIC COVER
IN UNASSEMBLED FORM.
BOM AS SHOWN IN TABLE

RoHS INFORMATION:
- THE LF PRODUCT MEETS EUROPEAN UNION
DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS+22-009
- THE PRODUCT IS NOT INTENDED TO BE EXPOSED
TO A MANUFACTURING SOLDER PROCESS

ITEM NO.	QTY.	PART DESCRIPTION
1	2	DTZK09 COVER
2	2	M3X12 COUNTERSUNK SCREW
3	1	D45ZK-D2 GROMMET SET
4	2	UNC 4-40X47 JACKSCREW

spec ref		-		dr		Dipu Joseph		2020/09/17		projection		mm		size		A3		scale		3:2	
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Detouillon, Da		2020/11/17						ecn no		-		rel level		Released	
ISO 406																					
ISO 1101																					
ISO 1101		chr		-		-		2020/11/13		product family		-		-		-		-		-	
surface		linear		0.X		±0.3		Amphenol FCI		title		DSUB METAL HOOD BLACK		dwg no		8655AMxxIAI1K00ILF		rev		A	
ISO 1302		0.XX		±0.10																	
ISO 1302		0.XXX		±0.005																	
ISO 1302		angular		0°		±2°		cat. no.		-		Product - Customer Drw		sheet 1 of 4							

PART NUMBER	PACK	HOOD SIZE
8655AMATIAI1K00ILF	KIT	15








GROMMET SET

ITEM NO.	QTY.	PART DESCRIPTION
1	2	DTZKI5 COVER
2	2	M3X12 COUNTERSUNK SCREW
3	1	D45ZK-D2 GROMMET SET
4	2	UNC 4-40X47 JACKSCREW


spec ref	-	dr	Dipu Joseph	2020/09/17	projection	mm	size	A3	scale	3:2
tolerance std	ISO 406 ISO 1101	eng	Detouillon, Da	2020/11/17	chr	-	ecn no	-	rel level	Released
surface	linear	appr	Wollin, Severi	2020/11/13	product family	-	rel level	Released	rev	A
ISO 1302	angular	0°	±2°	Amphenol FCi	DSUB METAL HOOD BLACK	cat. no.	-	Product - Customer Drw	sheet 2 of 4	

PART NUMBER	PACK	HOOD SIZE
8655AMBTIAI1K00ILF	KIT	25




GROMMET SET

ITEM NO.	QTY.	PART DESCRIPTION
1	2	DTZK25 COVER
2	2	M3X12 COUNTERSUNK SCREW
3	1	D45ZK-D2 GROMMET SET
4	2	UNC 4-40X47 JACKSCREW

spec ref -		dr Dipu Joseph		2020/09/17		projection 	mm 	size A3	scale 1:1
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED		eng Detouillon, Da	2020/11/17				ecn no -	rel level Released
			chr -	-					
			appr Wollin, Severi	2020/11/13					
product family -									
surface  ISO 1302	linear	0.X	±0.3	Amphenol FCI	title DSUB METAL HOOD BLACK	dwg no 8655AMxxIAI1K00ILF	rev A		
		0.XX	±0.10						
		0.XXX	±0.005						
	angular	0°	±2°					cat. no. -	Product - Customer Drw

PART NUMBER	PACK	HOOD SIZE
8655AMCTIAI1K00ILF	KIT	37



ITEM NO.	QTY.	PART DESCRIPTION
1	2	DTZK37 COVER
2	2	M3X12 COUNTERSUNK SCREW
3	1	D45ZK-D2 GROMMET SET
4	2	UNC 4-40X47 JACKSCREW

spec ref	-	dr	Dipu Joseph	2020/09/17	projection	mm	size	A3	scale	1:1
tolerance std	ISO 406 ISO 1101	eng	Detouillon, Da	2020/11/17	chr	-	ecn no	-	rel level	Released
surface	linear	appr	Wollin, Severi	2020/11/13	product family	-	rel level	Released	rev	A
ISO 1302	angular	0°	±2°	Amphenol FCi	DSUB METAL HOOD BLACK	cat. no.	-	Product - Customer Drw	sheet 4 of 4	