**Part Number :** 359659213
**Product Description :** VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type B, Yellow, Glow-Wire Capable
**Series Number :** 35965
**Status :** Active
**Product Category :** Connector Housings



## Documents and Resources

### Drawings

359659213_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

351500000AS_ENG-000.pdf

351500000AS_KOR-000.pdf

PK-35965-001-001.pdf

351800400-001.pdf

351800600-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)6375-DC (05 Nov 2025) |
| EU RoHS | Compliant per EU 2015/863 |

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Connector Housings |
| Series | 35965 |
| Description | VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type B, Yellow, Glow-Wire Capable |
| Application | Power, Wire-to-Wire |
| Product Name | VersaBlade |
| UPC | 822350872652 |

### Agency

| | |
|---|---|
| CSA | LR19980 |
| UL | E29179 |

### Physical

| | |
|---|---|
| Circuits (maximum) | 2 |
| Color - Resin | Yellow |
| Gender | Plug |
| Glow-Wire Capable | Yes |

Downloaded from Arrow.com.

| | |
|---|---|
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Resin | PET/PC |
| Net Weight | 2.687/g |
| Number of Rows | 2 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 8.00mm |
| Pitch - Termination Interface | 8.00mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +110°C |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| VersaBlade Multi-Module Hybrid Receptacle Housings | 35180 |

### Use with Part(s)

| Description | Part Number |
|---|---|
| VersaBlade Terminal Position Assurance (TPA) Retainer, 8.50mm Pitch, 2 Circuits, Red | 1040810282 |
| VersaBlade Terminal Position Assurance (TPA) Retainer, 8.00mm Pitch, 2 Circuits, Natural | 359650290 |
| VersaBlade Terminal Position Assurance (TPA) Retainer, 8.00mm Pitch, 2 Circuits, Red | 359650292 |
| VersaBlade Terminal Position Assurance (TPA) Retainer, 8.00mm Pitch, 2 Circuits, Yellow | 359650293 |
| VersaBlade Terminal Position Assurance (TPA) Retainer, Upper Type, 8.50mm Pitch, 3 Circuits, Red | 495470392 |

Downloaded from Arrow.com.

| | |
|---|---|
| VersaBlade Terminal Position Assurance (TPA) Retainer, Lower Type, 8.50mm Pitch, 3 Circuits, Natural | 495480390 |
| VersaBlade Male Crimp Terminal, 24-22 AWG, Type C | 2270288400 |
| VersaBlade Male Crimp Terminals | 35745 |



Downloaded from Arrow.com.