Part number

MFOE 16.32M



Hood, E-Xtreme® V-TYPE series, with 4 pegs, M32 side cable entry without adapter, size 77.27, high construction

Product description	
Product type	Hood
Series	E-Xtreme® V-TYPE
Closing type	With 4 pegs
Size	Size 77.27
Cable entry	Side cable entry M32
Specification	High construction
Technical data	
IP degree of protection	IP66 / IP67 / IP69
Further technical details	
Weight	220,00 g
Operating temperature range (min, max)	-40°C...+125°C


Material properties	
Colour	RAL 7016 grey
RoHs conformity	Compliant
China RoHs - EFUP	E
REACH SVHC substances	No
Approvals / Standards	
Certifications	CQC, DNV, BV
UL	ECBT2
cUL	ECBT8
General ordering information	
EAN13 code	8015747244145
eCl@ss 8.1	27440202
ETIM 7.0	EC000437
Packaging Information	
Sub-packaging weight	1,10 kg
Sub-packaging description	Plastic packaging
Sub-packaging quantity	5 Pcs
Sub-packaging EAN barcode	8015747244206

Downloaded from Arrow.com.

Part number

MFOE 16.32M

Catalogue drawings



Notes

Dimensions shown in mm are not binding and may be changed without notice.

Downloaded from Arrow.com.