



# PENA13CARTRIDGE, Oxide Inhibitor, Cartridge

By Burndy  
Catalog # PENA13CARTRIDGE

Cartridge for PENETROX A-13.



## Application

For Aluminum To Copper, Aluminum To Aluminum, Aluminum To Conduit

## General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Catalog Number	PENA13CARTRIDGE
Container Type	Cartridge
EU RoHS Indicator	Yes
Pour Point	-40 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
Type	A13
UPC	781810365519
UPC 12 Digit	7818103655199
Viscosity at 100 Fahrenheit	250 °F

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Container Size	1 lb
Minimum Pack Quantity	1

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_PENA13QT\\_LineArt](#)
- [Sales Drawings - 50008001](#)
- [SDS - PENETROX A-13 ESPANOL SDS](#)
- [SDS - PENETROX A-13 PORTUGUESE SDS](#)
- [SDS - PENETROX A-13 GERMAN SDS](#)
- [SDS - PENETROX A-13 SDS](#)
- [SDS - PENETROX A-13 ITALIAN SDS](#)
- [SDS - PENETROX A-13 FRENCH SDS](#)
- [Specifications - PENA13CARTRIDGE](#)

