Part Number : 731626161
Product Description : 4.3-10 Plug, Right-Angle, Wrench Tight, Solder, for 1/2" Super Flexible Coaxial Cable, One Piece Per Carton, 50 Ohms
Series Number : 73162
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

731626161_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-89675-210-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73162
Description	4.3-10 Plug, Right-Angle, Wrench Tight, Solder, for 1/2" Super Flexible Coaxial Cable, One Piece Per Carton, 50 Ohms
Application	Telecommunications/Networking, RF
Product Name	4.3-10
Style	Cable
Type	Medium
UPC	889056697675

Electrical

Frequency	12 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 1800 Vrms@Sea Level

Physical

Cable Attachment	Solder
Gender	Plug
Keying to Mating Part	N/A
Net Weight	134.500/g
Orientation	Right Angle
Packaging Type	Individual Carton
Panel Mount	No

Downloaded from Arrow.com.

Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	1/2" Super Flex Coaxial

Downloaded from Arrow.com.